




Ferroperm™ Piezoelectric

Pz21 Very soft relaxor type PNN-PZT



Microstructure of Pz21 at a magnification of 5000 times

A very soft relaxor based PNN-PZT solid solution

Pz21 is a very soft piezoceramic material with very high coupling factors and charge coefficients. The material is optimised for applications where high sensitivity, low porosity and small grain size are required.

Repeatable performance

The main focus through our entire production process is to provide materials and components with the highest possible reproducibility of properties and parameters and to obtain the lowest aging rates in the industry.

Our materials have a variation of $\pm 5\%$ for all parameters. This reduces the requirements for impedance matching, frequency tuning and dimensioning of the housing meaning fewer rejects and lower costs.

Customised solutions

We have more than 60 years of experience in the production of advanced piezoelectric ceramics. Our team has extensive expertise in customising designs to match the customer's needs.

Please contact us to discuss your requirements in further detail.

Key benefits

- Lowest batch to batch variation in the industry
- Stable material with consistent performance
- Customised or standard designs

Key features

- High sensitivity
- Low porosity
- Small grain size

Applications

- 1D, 2D, 3D medical arrays for imaging systems
- Shear Inkjet print heads
- Underwater acoustic sensors
- High precision flow meters

Contact

CTS Ferroperm

Porthusvej 4, DK-3490
Kvistgaard
Denmark
Tel: +45 49 12 71 00

e-mail: pz@actscorp.com

www.ferropermpiezoceramics.com

CTS Ferroperm

Our product competencies and services:
Piezoelectric ceramics | Multilayer | Thick-film | InSensor® | PiezoPaint™




Ferroperm™ Piezoelectric

Pz21 Very soft relaxor type PNN-PZT


Material properties

Electrical	Symbol	Pz21
Relative dielectric permittivity at 1 kHz	K_{33}^T	3800
Dielectric dissipation factor at 1 kHz	$\tan \delta$	17×10^{-3}
Curie temperature	T_C	$\sim 220^\circ\text{C}$
Recommended working range	\lesseqgtr	$\sim 130^\circ\text{C}$
Electromechanical		
Coupling factors	k_p	0.60
	k_t	0.47
	k_{33}	0.69
Piezoelectric charge coefficient	d_{33}	650 pC/N
Mechanical		
Mechanical Quality Factor	$Q_{m,P}^E$	65
Density	ρ	7.80 g/cm ³

Note: Due to continuous process improvement, specifications are subject to change without notice. Please be aware that extreme dimensions and geometries can lead to exaggeration in tolerances in all materials.



Permittivity (blue) and dielectric loss factor (red) for Ferroperm Pz21. The Curie point is above 220°C and the increase in permittivity in the recommended working range from 20° to 130°C is only 0.26% per °C.



Planar coupling factor (blue) and planar frequency constant (red) for Ferroperm Pz21 as a function of temperature. Very linear and stable behaviour is observed within the recommended working temperature range between 20°C and 130°C.

CTS Ferroperm

Our product competencies and services:
Piezoelectric ceramics | Multilayer | Thick-film | InSensor® | PiezoPaint™